



designed for scientists



RV 3 with Dry Ice Condenser, coated

/// Data Sheet

The RV 3 Rotary Evaporator is the manual basic model in the family of IKA Rotation Evaporators. It finds a multitude of uses in the chemical, pharmaceutical, and biotechnology industries, in research and development, in manufacturing and quality assurance, in laboratories, and in plant construction. Digital displays for speed and heating bath temperature enable optimum control of all distillation processes.

New: 4 liter heating bath
integrated safety lift-out function in case of power failure
water heating bath with carrying handles



designed for scientists

locking button for fixing heating bath temperature
locking mechanism: red indicator shows unlocked position of the vapor tube
flask clamping mechanism with integrated push-off function for easy exchange of evaporation flasks
manual lift for precise positioning of the glassware
adjustable immersion angle
single-handed manual lift handling, suitable for left and right-handed operators
speed range: 5 - 300 min⁻¹
low device voltage (24V) ensures user safety
compatible with the entire range of IKA RV 10 glassware

Package description: With heating bath HB eco and RV 10.40 dry ice condenser coated glassware set



designed for scientists

Technical Data

Type of cooling	vertical
Cooling surface [cm ²]	1500
Motor principle	DC
Speed range [rpm]	20 - 300
Speed tolerance set rotation speed < 100rpm [±rpm]	1
Speed tolerance set rotation speed > 100rpm [±%]	1
Lift	manual
Stroke [mm]	150
Heating temperature range [°C]	room temp. - 99
Dimensions (W x H x D) [mm]	440 x 530 x 330
Weight [kg]	28.3
Permissible ambient temperature [°C]	5 - 40
Permissible relative humidity [%]	80
Protection class according to DIN EN 60529	IP 20
Voltage [V]	100 - 240
Frequency [Hz]	50/60
Power input [W]	1400

